



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVOLUTIONS		DCP NO.	SPC-F005	Effective:	7/8/02	DCP No:	1398	
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
522	B	RELEASED	JWM	12/10/98	JC	1/8/99	JC	1/8/99
1258	C	UPDATED TO TABULAR SPEC	HO	7/16/02	JWM	7/16/02	JWM	7/16/02



- SPECIFICATION:**
- Shell: Steel, Nickel-Plated
 - Contact: Brass, Gold-Plated
 - Insulator: PBT & Glass-Fibre Reinforced, UL94V-0, Blue
 - Current Rating: 5 Amp
 - Dielectric Strength: 1000V for One Minute
 - Insulator Resistance: 1000 Meghoms Min. (at 500V DC)
 - Temperature: -55°C to +105°C

SPC TYPE NO.	NO. OF PINS	A	B	C	D	E	F	G	H
SPC4182	14	12.96 [0.510]	25.60 [1.007]	38.10 [1.500]	29.00 [1.142]	8.50 [0.335]	21.30 [0.838]	39.90 [1.570]	7.0 [0.275]
SPC4183	24	23.76 [0.935]	36.30 [1.429]	48.80 [1.921]	39.90 [1.570]	8.30 [0.327]	21.00 [0.826]	39.60 [1.559]	9.0 [0.354]
57-30360	36	36.72 [1.446]	49.30 [1.941]	61.80 [2.433]	53.20 [2.094]	7.90 [0.311]	22.60 [0.890]	40.00 [1.575]	11.5 [0.453]
SPC4184	50	51.84 [2.040]	64.40 [2.535]	77.00 [3.031]	68.10 [2.681]	8.60 [0.338]	24.90 [0.980]	44.30 [1.744]	12.5 [0.492]

DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

Tolerances Unless Otherwise Specified
 .X ±0.2 [0.008]
 .XX ±0.12 [0.005]

DRAWN BY:	DATE:
JEFF MCWICKER	12/10/98
CHECKED BY:	DATE:
APPROVED BY:	DATE:

DRAWING TITLE:		CENTRONIC CONNECTORS, MALE, WITH METAL HOOD	
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-536	TA-536.DWG	C
SCALE:	NTS	U.O.M.: [mm] INCHES	SHEET: 1 OF 1